



¹ d ₁	² d ₂	d ₃	l ₁	l ₂ min.
14	M 5	7	34	25
23	M 6	14	60	17
23	M 8	14	60	22
26	M 8	16	70	25
26	M 10	16	70	25
30	M 10	16	65	26
30	M 12	16	65	26
35	M 12	22	85	25
35	M 16	22	85	25

Specification

- Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 110 °C
- Black, shiny finish
- *Plastic Characteristics* → Page 2158
- **RoHS**

Information

When using elliptical shaped knobs GN 201, it must be ensured that the threaded stud is not too short. Otherwise, there is a risk that the duroplast plastic body could break under certain loads.

How to order ¹ GN 201-30-M10	1	d ₁
	2	d ₂

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

