



1.1

1.2

1.3

1.4

1

2

d_1	d_2	d_3	l_1	l_2
12	M 4	9	40	8
15	M 5	11	50	7
18	M 6	13	64	8
21	M 6	15	72	10
21	M 8	15	72	10
25	M 8	17	90	10
26	M 10	20	100	12
33	M 12	25	124	14

2.1

Specification

- Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 110 °C
- Black, shiny finish
- Spindle
Steel
Zinc plated, blue passivated
- *Plastic Characteristics* → Page 2158
- RoHS

Information

Fixed conical handles GN 203 are suitable for applications where the handle is exposed to low loads. For applications with increased loads we recommend to use cylindrical handles GN 539.

2.2

2.3

2.4

How to order

GN 203-15-M5

1	d_1
2	d_2

