



**3 Type**

- N** Angled lever with threaded bore
- L** Angled lever with plain bore H7

<b>1</b> $d_1$	<b>2</b> $d_2$ Thread	<b>2</b> $d_3$ H7 Bore	<b>b</b>	$d_4 \approx$	$d_5$	$h \approx$	$l_1$	$l_2 \approx$
10	M 8	-	11	12,5	16	26	50	48
13	M 10	B 10	14	16	20	32	63	60
16	M 12	B 12	17,5	20	25	40	80	76
20	M 16	B 16	23	25	32	51	100	95
25	M 20	-	30	31	40	63,5	125	119

**Specification**

- Steel
  - Turned
  - Blackened
- *ISO Fundamental Tolerances* → Page 2151
- **RoHS**

**On request**

- Short clamping levers with straight lever

How to order

**GN 204-16-M12-N**

- 1**  $d_1$
- 2**  $d_2$  ( $d_3$ )
- 3** Type

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

