



2 Bore code

- B** Without keyway
- K** With keyway
- V** With square

1

3

d ₁	d ₂ Bore H7 Square H11	d ₃	d ₄	d ₅	h ₁	h ₂	h ₃ ≈	Length l ≈
50	12	28	8	20	26	9	53	82
55	14	30	10	25	28	10	61	96
60	15	32	10	25	30	11	64	96
65	16	35	12	30	32	12	71	110
72	18	40	12	32	36	14	80	124
80	20	44	14	35	40	16	89	138
100	24	54	16	40	52	24	113	170

Specification

- Steel
Blackened
- Ball knobs DIN 319
Plastic, Duroplast
Black, shiny finish
- Keyway P9 DIN 6885 Page 1 → Page 2078
- Squares DIN 79 → Page 2082
- ISO Fundamental Tolerances → Page 2151
- RoHS

How to order

GN 213-65-B16

1	d ₁
2	Bore code
3	d ₂