



¹ d ₁	² Length l ±0,25	d ₂	h
8	30	12	26
10	40	15	31

Specification

- **GN 224.1**
Steel
Chrome-plated ● CR
Location disks
Zinc die casting, nickel-plated
- **GN 224.5**
Stainless steel AISI 304
Matte shot-blasted
Location disks
Stainless steel AISI 303
- *Stainless Steel Characteristics* → Page 2166
- RoHS

How to order (Steel) GN 224.1-8-30-CR	¹ b ₁
	² l ₁
	³ Finish

How to order (Stainless steel) GN 224.5-10-40	¹ d ₁
	² Length l