

STAINLESS*

1	2		
d_1	Length **l** ±0,25	**d_2**	**h**
8	30	12	26
10	40	15	31

Specification

GN 224.1
Steel
- Chrome plated — **CR**
- Location disks
  Zinc die casting, nickel plated

GN 224.5
Stainless steel AISI 304
- Matte, shot blasted
- Location disks
  Stainless Steel AISI 303

RoHS

see also...	Page
GN 224.3 Finger Handles (Plastic)	QVX

Technical Information

Stainless Steel Characteristics	QVX

How to order (Steel)
1 2 3
GN 224.1-8-30-CR

1	d_1
2	Length l
3	Material

How to order (Stainless steel)
1 2
GN 224.5-10-40

1	d_1
2	Length l