



1.1

1.2

1.3

1.4

d ₁	Length l		d ₂ Bore B	d ₃	h
	Nominal dimension	Actual dimension			
9	30	29,5	B 3,5	12	27
10	40	39,5	B 3,5	15	33,5

2.1

Specification

- Plastic
Technopolymer (Polyamide PA)
Temperature resistant up to 100 °C

• Colors (matte finish):

- Black, RAL 9005 **SW**
- Orange, RAL 2004 **OR**
- Gray, RAL 7035 **GR**
- Red, RAL 3000 **RT**
- White, RAL 9002 **WS**

• *Plastic Characteristics* → Page 2158

• **RoHS**

4

Information

Finger handles GN 224.3 with bore hole B 3,5 are intended for fixing with self-tapping screws of thread size ST 4,2 such as DIN ISO 7049 pan head tapping screws.

2.2

2.3

2.4

How to order

1	d ₁
2	Length l
3	d ₂
4	Color

GN 224.3-10-40-B3,5-SW

