



- 2 Coding**
- MCR** Matte chrome plated
- MCRS** Matte chrome plated, standard scale 0...90, 100 graduations, acc. scale scheme d₇/100 A RA 0-10 20...90/10

1

d ₁	d ₂	d ₃ H7	d ₄	l ₁	l ₂	Scaling set consists of: 1 Scale ring GN 264	
						2 collar bushings	3 flat springs
30	27	24	33	16	23,7	GN 268-24-K...	GN 374-0,3-10
40	36	32	43	16	23,7	GN 268-32-K...	GN 374-0,4-10
60	55	50	63	16	25,7	GN 268-50-K...	GN 374-0,6-10
80	75	68	83	16	25,7	GN 268-68-K...	GN 374-0,8-10

Specification

- Steel
- Scale lug d₁ fine turned
- Plain (standard version)
- Matte chrome plated
- Matte chrome plated with standard scale
- Scale engraved with laser precision, black
- ISO Fundamental Tolerances → Page 2151
- RoHS

2

Information

Besides the standard scale (coding MCRS) the scale rings can be supplied with any type of graduation. It is suggested to use the matte chrome plated version (MCR) so that a nice discrepancy in color is given.

Regarding design, numbering run, numbering position and numbering sequence of the scale please see the layout for scale rings on the order sheet „How to Order Graduations“ → Page 326.

see also...

- Collar Bushing GN 268 → Page 330
- Flat Springs GN 374 → Page 330
- Scale Rings GN 164 (with and without Scale) → Page 327

On request

- Special graduations see „How to Order Graduations“ → Page 326

How to order (Scale ring without scale)	1	d ₁
GN 264-80		

How to order (Scale ring with scale)	1	d ₁
GN 264-40-MCRS	2	Coding