



| ¹ d ₁ Bore for sensor | ² b Swivel width | d ₂ | d ₃ | Length l | m ₁ | m ₂ | t ₁ | t ₂ | x ₁ | x ₂ | y ₁ | y ₂ |
|---|-----------------------------------|----------------|----------------|----------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|
| B 18 | 40 | 50 | 6,5 | 52,5 | 32,5 | 30 | 10 | 7 | 60 | 42 | 60 | 42 |
| B 30 | 40 | 50 | 6,5 | 52,5 | 32,5 | 30 | 10 | 7 | 60 | 42 | 60 | 42 |

Specification

- Aluminum
- Powder coated
- Black, RAL 9005, textured finish ● **SW**
- RoHS

³

Information

Sensor holders GN 272.4 accept sensors with external thread via the hole in the lug.

see also...

- Universal Work Holding and Positioning Fixtures GN 177 (for Work Gripper Blocks GN 177.1) → Page 1806
- Attachment Mounting Clamps GN 478 (for Sensor Holders GN 479) → Page 1795

How to order

GN 272.4-B30-40-SW

| | |
|--------------|----------------|
| ¹ | d ₁ |
| ² | b |
| ³ | Finish |

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

