



2 Type

S Steppless adjustment

3 Identification no.

2 With 5 stainless steel socket cap screws DIN 912

d ₁ - d ₂ Bore - Bore	d ₁ - s ₂ Bore - Square	s ₁ - s ₂ Square - Square	b Swivel width	k	l ₁	l ₂	m	z ₁ Screw locations	z ₂ Screw location	Accessory Recom. hand lever GN 911			
										für z ₁ l ₃		für z ₂ l ₃	
B40 - B40	B40 - V40	V40 - V40	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B40 - B42	B40 - V45	-	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B40 - B45	B40 - V50	V40 - V45	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B40 - B48	B42 - V40	-	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B40 - B50	B42 - V45	V40 - V50	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B42 - B42	B42 - V50	-	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B42 - B45	B45 - V40	-	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B42 - B48	B45 - V45	V45 - V45	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B42 - B50	B45 - V50	-	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B45 - B45	B48 - V40	V45 - V50	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B45 - B48	B48 - V45	-	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B45 - B50	B48 - V50	-	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B48 - B48	B50 - V40	-	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B48 - B50	B50 - V45	-	65	76	268	70	85	M10-60	M10-55	78	92	78	92
B50 - B50	B50 - V50	V50 - V50	65	76	268	70	85	M10-60	M10-55	78	92	78	92

Specification

- Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish ● **SW**
 - Plain, matte shot-blasted ○ **BL**
- Socket cap screws DIN 912
Stainless steel AISI 304
- Hex nuts DIN 985
Stainless steel AISI 304
Self-locking via polyamide ring
- Stainless Steel Characteristics → Page 2166
- RoHS

Accessory

- Adjustable Hand Levers GN 911 → Page 1784

Information

Swivel clamp connector joints GN 289 are an assembly of two swivel clamp connectors GN 279.

The square versions are also suitable for use with **profile systems**.

The clamping bores are not machined and are designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462.

At the screw locations **z₁**, the socket cap screws reduce the cross-section for clamping.

For clamping without tools, the socket cap screws can be replaced by the adjustable hand levers GN 911 listed in the table as accessory.

How to order	
1	d ₁ - s ₂ (d ₁ - d ₂ , s ₁ - s ₂)
2	Type
3	Identification no.
4	Finish

GN 289-B40-V40-S-2-BL

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9