



¹ d ₁ Bore Clamp connector	² d ₂ Bore				³ Length l
18	B 12	B 14	B 15	B 16	29
30	B 20	B 25	-	-	45

Specification

- Plastic Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 100 °C
 - Black, RAL 9005, matte finish **● SW**
 - Gray, RAL 7040, matte finish **● GR**
- [Load Rating Information](#) → Page XYZ
- [Plastic Characteristics](#) → Page XYZ
- [RoHS](#)



Information

Adapter bushings GN 290 can be used to reduce the bore diameter of plastic clamp connectors for clamping smaller diameters.

Due to the affixed swivel limiting stop, the adapter bushing cannot rotate or slide inside the clamp connector.

see also...

- [Plastic Clamp Connectors](#) → Page XYZ ff.
- [Construction Tubes GN 990](#) → Page XYZ

How to order	
¹	d ₁
²	d ₂
³	Length l
⁴	Color

GN 290 - 30 - B20 - 45 - SW

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

