



1 2

l_1	d_1	d_2	d_3	d_4	h_1	h_2	h_3	h_4 Stroke	t min.
63	M 6	14	14,8	19	43,8	16,3	60,1	2,5	10
63	M 8	18	18,8	19	45,8	18,3	62,1	2,5	12
78	M 8	18	18,8	24	49,3	16,5	69,3	3	12
78	M 10	22	22,8	24	51,3	18,5	71,3	3	15

Specification

- Handle
Stainless steel
precision casting AISI 316
Polished finish ($R_a < 0.8 \mu m$) **PL**
- Threaded bushing
Stainless steel AISI 304
- Sealing ring / Wiper **H E**
 - H-NBR
Temperature resistant $-25 \text{ }^\circ\text{C}$ to $+150 \text{ }^\circ\text{C}$
 - EPDM
Temperature resistant $-40 \text{ }^\circ\text{C}$ to $+120 \text{ }^\circ\text{C}$
 - Blue
 - Hardness 85 ± 5 Shore A
 - FDA compliant
- Plastic Characteristics → Page 2158
- Stainless Steel Characteristics → Page 2166
- RoHS

3 4

Information

Adjustable hand levers GN 305 with solid stainless steel handle comply with the DGVV testing principles, making them suitable for use in hygienic areas.

The sealed mounting surface enables fastening without dead spaces. The high quality finish as well as the impervious exterior surfaces prevent adherence of dirt and facilitate cleaning.

Adjustable hand levers are ideal whenever parts have to be clamped in a confined space or in a particular lever position.

The threaded insert is moveably attached to the handle with serrations. When pulling the handle, the serration frees itself and can be re-located into any required position. Engagement is achieved by releasing the lever.

see also...

- Product Family *Hygienic Design* → Page 16
- Star Knobs GN 5435 (Stainless Steel, *Hygienic Design*) → Page 581
- Three Knob Handles GN 5445 (Stainless Steel, *Hygienic Design*) → Page 593

Accessory

- Sealing Rings GN 7600 → Page 1596

How to order	
1	l_1
2	d_1
3	Finish
4	Material (Sealing ring)

GN 305-63-M8-PL-H