



STAIN  
LESS  
\*

4 Type

C With thread

K With plain hole H7

d <sub>1</sub>	d <sub>2</sub> Type C Thread	d <sub>3</sub> H7 Type K Bore	d <sub>4</sub> ≈	h ≈	t <sub>1</sub> min.	t <sub>2</sub> min.
16	M 4	B 6	8	15	7	9
20	M 5	B 8	12	18	9	11
25	M 6	B 10	15	22,5	11	14
32	M 8	B 12	18	29	14,5	17
40	M 10	B 16	22	37	18	22
50	M 12*	B 20	27	46	21	28

\* This size is only available in steel and aluminum.

Specification 1

Steel Polished **ST**

Aluminum Polished **AL**

Stainless steel AISI 303 Matte shot-blasted **NI**

RoHS

Ball knobs DIN 319 made of steel, aluminum and stainless steel are not on the official DIN standard sheet.

see also...	Page
DIN 319 Ball Knobs (Plastic)	QVX

Technical Information	
ISO Fundamental Tolerances	QVX
Stainless Steel Characteristics	QVX

How to order	
1 Material	
2 d <sub>1</sub>	
3 d <sub>2</sub> (d <sub>3</sub> )	
4 Type	

DIN 319-AL-40-M10-C

