



1 2

| b <sub>1</sub> | l <sub>1</sub> ±0,5             | a  | b <sub>2</sub> | d   | h <sub>1</sub> | h <sub>2</sub> | l <sub>2</sub> | t min. |
|----------------|---------------------------------|----|----------------|-----|----------------|----------------|----------------|--------|
| 36             | 200 250 300 350 400 500 600 800 | 24 | 22             | M 8 | 57             | 71             | 40             | 15     |

Specification

- Handle tube  
Aluminum
- Handle legs  
Zinc die casting  
Powder coated
- Tube ● SW  
Powder coated  
Black, RAL 9005, textured finish  
Handle legs  
Black, RAL 9005, textured finish
- Tube ● EL  
Anodized, natural color  
Handle legs  
Black, RAL 9005, textured finish
- Tube ● ES  
Anodized, natural color  
Handle legs  
Silver, RAL 9006, textured finish
- Cover  
Plastic, light gray
- Load Rating Information → Page 2106
- RoHS

3

Information

Oval tubular handles GN 334 are attractive in design and highly stable. The handle tube can be mounted without any further machining, allowing **special lengths** to be realised easily.

How to order

GN 334-36-300-EL

- 1 b
- 2 l<sub>1</sub>
- 3 Finish