



<b>d<sub>1</sub></b>	<b>Length l</b>					<b>d<sub>2</sub></b>	<b>d<sub>3</sub></b>	<b>h<sub>1</sub></b>	<b>h<sub>2</sub></b>	<b>r</b>	<b>t<sub>min.</sub></b>
	55*	64	88*	96	100						
8	55*	64	88*	96	100	M 4	12	40	30	9	8
10	88*	100	120*	180*	200	M 5	15	47	35	11	12
12	125	160	200	250	-	M 6	-	60	44	12	12

\* suitable for 19" rack and enclosure layout

**Specification**

- Steel
  - Powder coated
    - Black, RAL 9005, textured finish **● SW**
    - Chrome-plated **● CR**
    - Blackened **● BT**
- Location disks
  - Zinc die casting, nickel plated
- Load Rating Information → Page 2106
- RoHS

**Accessory**

- Fastening Sets GN 181  
(Mounting from the Operator's Side)  
→ Page 160

**Information**

Cabinet U-handles GN 425.1 are manufactured from a bent steel profile. Cabinet U-handles with  $\varnothing d_1 = 8$  and 10 are delivered with two location disks to ensure proper contact of the handle even in the case of large connecting holes. The disks are loosely enclosed.

The stainless steel version is preferred over the chrome-plated version in steel for outdoor applications.

see also...

- Cabinet U-Handles GN 425 (Steel, not Angled) → Page 146

How to order

**GN 425.1-10-100-CR**

<b>1</b>	<b>d<sub>1</sub></b>
<b>2</b>	<b>Length l</b>
<b>3</b>	<b>Finish</b>