



d ₁	Length l					d ₂	d ₃	h ₁	h ₂	r	t min.
8	55*	64	88*	96	100	M 4	12	40	30	9	8
10	88*	100	120*	180*	200	M 5	15	47	35	11	12
12	125	160	200	250	-	M 6	-	60	44	12	12

* suitable for 19" rack and enclosure layout

Specification

Stainless steel	NI	
<ul style="list-style-type: none"> AISI 303 for d₁ = 8, 10 AISI 304 for d₁ = 12 Matte shot-blasted finish Electropolished Location disks Stainless Steel AISI 303	GS	EP
Stainless steel AISI 316L	A4	
<ul style="list-style-type: none"> Matte shot-blasted finish Location disks Stainless Steel AISI 316L	GS	
Aluminum	AL	
<ul style="list-style-type: none"> Plastic coated Black, RAL 9005, textured finish Silver, RAL 9006, textured finish Red, RAL 3000, textured finish Anodized, natural color Location disks Zinc die casting, nickel plated 	<ul style="list-style-type: none"> ● SW ● SR ● RS ● EL 	

RoHS

Cabinet U-handles GN 425.1 are manufactured from a bent stainless steel or aluminum profile. Cabinet U-handles with Ø d₁ = 8 and 10 are delivered with two location disks to ensure proper contact of the handle even in the case of large connecting holes. The disks are loosely enclosed. The stainless steel version is preferred over the chrome-plated version in steel for outdoor applications.

see also...	Page
GN 425.1 Cabinet U-Handles (Steel)	QVX
GN 425 Cabinet U-Handles (Aluminum / Stainless Steel, not angled)	QVX

Technical Information

Load Rating Information	QVX
-------------------------	-----

Accessory

GN 181 Fastening Sets (Mounting from the Operator's Side)	QVX
---	-----

How to order (Aluminum)

1	Material
2	d ₁
3	Length l
4	Finish

1 2 3 4
GN 425.1-AL-12-125-EL

How to order (Stainless steel)

1	Finish
2	d ₁
3	Length l
4	Finish

1 2 3 4
GN 425.1-NI-10-180-GS