



1 2

d <sub>1</sub>	l <sub>1</sub> ±0,5	l <sub>2</sub>	b	d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	t min.
10	120	94	16	M 5	18	53	43	8	24	12
10	180	94	16	M 5	18	56	43	8	24	12

**Specification**

- Steel  
Matte chrome-plated
- Plastic handle  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 150 °C  
- Black, matte finish
- *Plastic Characteristics* → Page 2158
- RoHS

**Information**

Cabinet U-handles GN 425.7 made of steel feature a plastic grip which, owing to its insulating properties, allows it to be used under high surface temperatures.

The above temperature distribution curve has been measured at a surface temperature of 200 °C and a room temperature of 23 °C.

see also...

- *Cabinet U-Handles GN 425 (Steel)* → Page 147

How to order

**GN 425.7-10-120**

1 d<sub>1</sub>

2 l<sub>1</sub>

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

