



d ₁			Length l							d ₂	d ₃	h	r	t min.
NI	A4	AL	32	45	55*	64	88*	-	-	M 3	9	26	7	6
6	-	-	32	45	55*	64	88*	-	-	M 3	9	26	7	6
8	-	8	55*	64	88*	96	100	120*	128	M 4	12	35	10	8
10	10	10	88*	100	120*	180*	200	235*	-	M 5	15	43	12	12
12	-	12	125	160	200	250	-	-	-	M 6	-	51	14	12
16	-	16	160	200	250	300	-	-	-	M 6	-	59	18	12

* suitable for 19" rack and enclosure layout

Specification

<p>Stainless steel</p> <p>AISI 303 for d₁ = 6, 8, 10</p> <p>AISI 304 for d₁ = 12, 16</p> <ul style="list-style-type: none"> • Matte shot-blasted finish • Electropolished • Location disks for d₁ = 6, 8, 10 <p>Stainless steel AISI 303</p>	<p>NI</p> <p>GS</p> <p>EP</p>
<p>Stainless steel AISI 316L</p> <ul style="list-style-type: none"> • Matte shot-blasted finish • Location disks <p>Stainless steel AISI 316L</p>	<p>A4</p> <p>GS</p>
<p>Aluminum</p> <ul style="list-style-type: none"> • Powder coated - Black, RAL 9005, textured finish - Silver, RAL 9006, textured finish - Red, RAL 3000, textured finish • Anodized, natural color • Location disks for d₁ = 8, 10 • Zinc die casting, nickel plated 	<p>AL</p> <p>SW</p> <p>SR</p> <p>RS</p> <p>EL</p>

RoHS

Cabinet U-handles GN 425 are manufactured from a bent stainless steel or aluminum profile. Cabinet U-handles with Ø d₁ = 6, 8 and 10 are delivered with two location disks to ensure proper contact of the handle even in the case of large connecting holes. The disks are loosely enclosed.

see also...

GN 425 Cabinet U-Handles (Steel)	QVX
GN 425.1 Cabinet U-Handles (Aluminum / Stainless Steel, Angled)	QVX
GN 427 Cabinet U-Handles (Aluminum, Ellipse Shaped Profile)	QVX

Technical Information

Load Rating Information	QVX
Stainless Steel Characteristics	QVX

Accessory

GN 181 Fastening Sets (Mounting from the Operator's Side)	QVX
--	-----

How to order (Aluminum)

1 Material
 2 d₁
 3 Length l
 4 Finish

GN 425-AL-8-88-EL

How to order (Stainless steel)

1 Material
 2 d₁
 3 Length l
 4 Finish

GN 425-A4-10-180-GS