







2	3					
d ₁	Length I ±0,25 SW / SR / BL	SMA / WSA	d ₂	h	r	t min.
20	200	200	M 8	68	22	15
20	250	250	M 8	68	22	15
20	300	300	M 8	68	22	15
20	350	-	M 8	68	22	15
28	250	250	M 10	78	32	15
28	300	300	M 10	78	32	15
28	350	-	M 10	78	32	15
28	400	400	M 10	78	32	15

Specification

- Aluminum
- Powder coated, textured finish Black, RAL 9005 SW Silver, RAL 9006 SR
- Powder coated, antimicrobial finish Black, RAL 9005 SMA White, RAL 9016 WSA
- BL - Plain, tumbled Load Rating Information → Page 2106
- RoHS

Information

Cabinet U-handles GN 426 are manufactured from a bent aluminum profile and have excellent stability and ergonomic design.

In addition to the standard surfaces, these cabinet U-handles are also available with a functional coating.

The SMA / WSA versions have a powder coating based on silver ions, which gives them antimicrobial properties. The principle of action has been shown to reduce the contamination of the handle surfaces within 24 hours so that fewer than 1% of bacteria and fewer than 5% of viruses ultimately survive.

Standard parts with antimicrobial plastic coating are primarily used in the health care sector and in public buildings, such as airports, train stations, stadiums, etc.

see also...

- Product Family Sanline → Page 2154
- Cabinet U-Handles GN 428 (Aluminum) → Page 163

How to order	1	Material
	2	d_1
	3	Length I
GN 426-AL-28-300-SW	4	Finish