



<sup>2</sup> d <sub>1</sub>	<sup>3</sup> Length l	d <sub>2</sub>	h <sub>1</sub> ≈	h <sub>2</sub> ≈	h <sub>3</sub>	r	t ≈
20	200	6,5	105	68	36	22	9
20	300	6,5	105	68	36	22	9
28	250	9	125	78	34	32	11
28	350	9	125	78	34	32	11
28	500	9	125	78	34	32	11

Specification

Aluminum

- Powder coated
  - Black, RAL 9005, textured finish
  - Silver, RAL 9006, textured finish
- Plain finish, tumbled

- <sup>1</sup> AL
- <sup>4</sup> SW
- SR
- BL

RoHS

Cabinet U-handles GN 426.4 are manufactured from a bent aluminum profile.

see also...

	Page
GN 426 Cabinet U-Handles (Mounting from the Back)	QVX
GN 426.6 Cabinet U-Handles (Stainless Steel, Angled, Mounting from the Back)	QVX
GN 426.1 Cabinet U-Handles (Angled, Mounting from the Back)	QVX
GN 426.2 Cabinet U-Handles (Mounting from the Operator's Side)	QVX
GN 426.5 Cabinet U-Handles (Stainless Steel, Mounting from the Back)	QVX

Technical Information

Load Rating Information	QVX
-------------------------	-----

How to order	
<sup>1</sup>	Material
<sup>2</sup>	d <sub>1</sub>
<sup>3</sup>	Length l
<sup>4</sup>	Finish

**GN 426.4-AL-20-200-BL**