



b	Length l ±0,25	a	h	r
12	55*	8	40	8
12	88*	8	40	8
12	100	8	40	8
12	120*	8	40	8
12	180*	8	40	8
12	200	8	40	8
12	235*	8	40	8

* suitable for 19" rack and enclosure layout

Specification

- GN 427**
 Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish ● **SW**
 - Silver, RAL 9006, textured finish ● **SR**
 - Anodized, natural color ● **EL**
- GN 427.5**
 Stainless steel AISI 304
 Matte shot-blasted
- *Load Rating Information* → Page 2106
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

Information

Cabinet U-handles GN 427 / GN 427.5 are manufactured from a bent aluminum / stainless steel profile.

see also...

- *Cabinet U-Handles GN 425 (Aluminum / Stainless Steel)* → Page 147

How to order (Aluminum)

GN 427-12-120-EL

- 1 **b**
- 2 **Length l**
- 3 **Finish**

How to order (Stainless steel)

GN 427.5-12-180

- 1 **b**
- 2 **Length l**