



b	Length $l \pm 0,25$	a	h	r
12	55*	8	40	8
12	88*	8	40	8
12	100	8	40	8
12	120*	8	40	8
12	180*	8	40	8
12	200	8	40	8
12	235*	8	40	8

* suitable for 19" rack and enclosure layout

Specification

- **GN 427**
Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish ● **SW**
 - Silver, RAL 9006, textured finish ● **SR**
 - Anodized, natural color ● **EL**
- **GN 427.5**
Stainless steel AISI 304
Matte shot-blasted
- *Load Rating Information* → Page 2106
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

Information

Cabinet U-handles GN 427 / GN 427.5 are manufactured from a bent aluminum / stainless steel profile.

Due to the manufacturing process, **special designs** can be supplied even in relatively small quantities.

see also...

- *Cabinet U-Handles GN 425 (Aluminum / Stainless Steel)* → Page 147

How to order (Aluminum)	1	b
	2	Length l
	3	Finish
GN 427-12-120-EL		

How to order (Stainless steel)	1	b
	2	Length l
GN 427.5-12-180		