



<sup>2</sup> d <sub>1</sub>	<sup>3</sup> d <sub>2</sub>	<sup>4</sup> Length l				b	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	t min.
20	M 4	6	10	-	-	9	8	8	3,5	7
26	M 4	12	16	-	-	11	10	10	4,5	7
26	M 5	10	12	16	-	11	10	10	4,5	8
26	M 6	12	16	20	25	11	10	10	4,5	8
34	M 6	16	20	25	30	13	12	12	5	10
34	M 8	16	20	25	30	13	12	12	5	9

**Specification**

- Stainless steel precision casting
  - AISI CF-8 **NI**
  - AISI 316 **A4**
  - Matte shot-blasted **MT**
- Stainless Steel Characteristics → Page 2166
- RoHS

**Information**

Wing screws GN 433 and wing nuts GN 434 clamp and fasten parts easily without tools. The ergonomic shape and the projecting collar make operation easier.

The version in stainless steel A4 can be used in especially aggressive environments.

see also...

- Wing Nuts GN 834 (Stainless Steel) → Page 618
- Wing Screws GN 835 (Stainless Steel) → Page 619
- Hand Knobs DIN 6335 (Stainless Steel) → Page 582

How to order (Wing nut)		1 Material
		2 d <sub>1</sub>
		3 d <sub>2</sub>
<b>GN 434-NI-26-M6-MT</b>		5 Finish

How to order (Wing screw)		1 Material
		2 d <sub>1</sub>
		3 d <sub>2</sub>
		4 Length l
<b>GN 433-NI-34-M8-20-MT</b>		5 Finish