



- 1
- 2
- 3

d <sub>1</sub>	l <sub>1</sub>	Wall thickness Nominal size	s	a Profile cross-section	b	d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	l <sub>5</sub>	l <sub>6</sub>	m <sub>1</sub>	m <sub>2</sub>
59	15	A 1	1...10	30	44	57	50	5,1	33	25	3,5	23	28	5	34	8	19,5	30	6,3
59	20	A 1	1...10	40	44	57	50	5,1	33	25	3,5	23	28	5	34	8	19,5	30	6,3

**Specification**

- Front body  
Plastic (Polyacetal POM)  
- Temperature resistant up to 60 °C  
- UV resistant
- Housing / snap element  
Plastic (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 60 °C  
- UV resistant
- Color  
Black, matte finish ● SW
- Self-tapping screws ISO 7049, ST 3.5-19  
Stainless steel
- *Plastic Characteristics* → Page QVX
- RoHS



**Information**

Snap latches GN 449.4 combine the function of a gripping tray with that of a snap latch to provide an easy way to keep doors and covers closed.

The mounting hole must be created according to the dimensions specified in the mounting information. For mounting, first insert the front body into the hole in the door, then push in the housing from the opposite side. Use the two supplied self-tapping screws to join the housing with the front body.

Finally, orient the snap element based on the reference marks and mount it on the frame or profile.

**see also...**

- *Spring-Bolt Door Latches GN 449.1* → Page QVX
- *Assembly Sets for Profile Systems 30 / 40 GN 965* → Page QVX
- *Assembly Sets for Profile Systems 30 / 40 / 45 GN 968* → Page QVX

How to order	
1	d <sub>1</sub>
2	l <sub>1</sub>
3	Nominal size
4	Color

**GN 449.4-59-15-A1-SW**

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9

