



Mounting information



- 2 Type**
- OS** Without lock
 - SC** With lock

1

d ₁	Wall thickness	b	d ₂	d ₃	h ₁	h ₂	h ₃	l ₁	l ₂	l ₃	l ₄ ≈	l ₅	l ₆	l ₇	l ₈	l ₉	m	w		
Nominal size	s																			Adjustable range
61	A 1	1...5	32	60	5,5	36	3	16,5	6,5	16	13	8	33,5	16	18	1,2	27,5	19,5	3	

Specification

- Latch / Catch**
Stainless steel AISI 304
 • Housing collar / Mounting ring / Opening handle
 Polished **PL**
 • Pan head screws
- Lock**
Stainless steel AISI 316
- Key**
Brass, nickel plated
- RoHS

Snap latches GN 449.5 combine the function of a gripping tray with that of a snap latch to provide an easy way to keep doors, covers and hoods closed. Once the mounting hole has been drilled, the housing is inserted into the hole in the door body when actuated and the mounting ring is pushed on from behind. The housing and mounting ring are connected with two supplied pan head screws.

The catch is mounted on the door profile or frame at a right angle to the snap element in accordance with the dimensions.

see also...	Page
GN 449.1 Spring-Bolt Door Latches	QVX
GN 449.4 Snap Latches (Plastic)	QVX

Technical Information

Stainless Steel Characteristics	QVX
---------------------------------	-----

How to order	
1 d ₁	
2 Type	
3 Finish	

GN 449.5-61-OS-PL