



¹ a _{-0.3} -0.5	² d	e	h	k	s	For T-slots DIN 650
10	M 8	15	12	6	0,65	10
12	M 10	18	14	7	0,65	12
14	M 12	22	16	8	1	14
18	M 16	28	20	10	1	18
22	M 20	35	28	14	1,6	22

Specification

- Heat-treated steel
- Property class
Zinc plated, blue passivated
- Property class
Blackened
- *Strength Values of Nuts* → Page 2152
- RoHS

Information

- ³ T-nuts GN 508.2 are dimensionally identical to DIN 508.
- 8** They are, however, fitted on the side with a spring loaded element (ball / pressure spring). This will prevent an unwanted movement of the nut, especially in a vertically mounted T-slot bed.
- 10** see also...
 - *T-Nuts GN 508* → Page 1162

How to order

GN 508.2-22-M20-10

¹	a
²	d
³	Property class