



1

2

d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	l <sub>1</sub>	l <sub>2</sub> min.	l <sub>3</sub> ±0,5
14	M 5	11	28	12	1,5
18	M 6	15	40	25	3,5
18	M 8	15	40	25	3,5
21	M 6	17	50	25	3,5
21	M 8	17	50	35	7,5
23	M 8	19	65	30	7,5
23	M 10	19	65	40	7,5
26	M 8	21	80	45	7
26	M 10	21	80	55	7
26	M 12	21	80	55	10
28	M 8	22	90	45	7
28	M 10	22	90	55	7
28	M 12	22	90	58	8
29	M 12	23	116	58	8
31	M 12	25	102	58	8

## Specification

- Plastic  
Duroplast (Phenolic PF)
  - Temperature resistant up to 110 °C
  - Black, shiny finish
- *Plastic Characteristics* → Page 2158
- RoHS

## Information

When using the cylindrical knobs GN 519, make sure that the threaded pin is not too short, otherwise the plastic element may break under excessive stress exposure.

see also...

- *Softline Cylindrical Knobs GN 519.6* → Page 73

How to order

GN 519-23-M8

1 d<sub>1</sub>

2 d<sub>2</sub>