



1.1

1.2

1.3

1.4

1

2

$d_1 + 0,5$	d_2 Color SW	Color RT	d_3	l_1	l_2 min.	l_3
24	M 8	M 8	20,5	65	30	7
24	M 10	-	20,5	65	40	7
26	M 8	-	21	80	40	7
26	M 10	M 10	21	80	55	7
26	M 12	-	21	80	55	7
28	M 10	-	22,5	90	58	7
28	M 12	M 12	22,5	90	58	7

Specification

3

- Plastic Technopolymer (Polyamide PA)
- Temperature resistant up to 110 °C
- Color (matte finish)
 - Black, RAL 9005
 - Red, RAL 3000



- ISO Fundamental Tolerances → Page 2151
- Plastic Characteristics → Page 2158

• RoHS

Information

Cylindrical knobs GN 519.2 are an advanced development of the Duroplast cylindrical knobs GN 519. Thanks to the polyamide material used in their manufacture, they feature superb mechanical properties.

see also...

- Cylindrical Handles GN 519.2 (Detectable Plastics) → Page 70
- Cylindrical Knobs GN 519.2 (Antibacterial Plastic) → Page 71
- Softline Cylindrical Knobs GN 519.6 → Page 73

2.1

2.2

2.3

2.4

How to order

GN 519.2-26-M10-RT

1	d_1
2	d_2
3	Color

