



3.1

Type C



Type **E**







Туре

C Open eye

E* Closed eye

2

Length I		b	d ₁		d ₂	d ₃	f	m	Static load
Type C	Type E	Type E	Type C	Type E	min.		min.	min.	in N ≈
40	-	-	6	-	11	4	4,5	5	500
50	50	5,3	8	6	15	5	5,5	7	1200
60	60	6,4	9	7	17	6	6,5	8	1200

* Only available in stainless steel

Specification



• Stainless steel A4
Plain finish BL

- Stainless Steel Characteristics → Page QVX
- RoHS

Accessory

Key Rings GN 111.3 → Page QVX

Information

Carabiners GN 5299 are used, for example, to connect tools or other components quickly and without tools or to secure them against loss. The carabiner is opened by hand and closes automatically by a concealed spring when released.

The eye of type E, which is fitted with a pressed-in, closed round thimble, enables captive mounting of the carabiners, e.g. by means of an appropriately pressed retaining cable.

Carabiners GN 5299 must not be used for lifting loads or lashing. The data on load capacity are approximate values to the exclusion of any liability.

see also...

- Retaining Cables GN 111.2 (Stainless Steel) → Page QVX
- Retaining Cables GN 111.8 (Stainless Steel AISI 316) → Page QVX
- Ball Chains GN 111 (Brass) → Page QVX
- Ball Chains GN 111.5 (Stainless Steel) → Page QVX
- Spiral Retaining Cables GN 111.4 (Plastic) → Page QVX

How to order	1	Туре
	2	Length I
1 2 3 4	3	Material
GN 5299-C-50-ST-ZB	4	Finish



3.6

3.7

3