



1 2 3

n	d	Steel						Stainless steel						b	h <sub>1</sub>	h <sub>2</sub>	l <sub>2</sub>
		16	20	25	30	40	60	20	25	30	40	60					
8	M 6	16	20	25	30	40	60	20	25	30	40	60	16	4,5	1,5	8	
8	M 8	20	25	30	-	-	-	-	-	-	-	-	16	4,5	1,5	8	
10	M 6	16	20	25	30	40	60	20	25	30	40	60	19,5	5,5	4	8,5	
10	M 8	20	25	30	40	60	-	20	25	30	40	60	19,5	5,5	4	8,5	

Specification

- Steel, zinc plated, blue passivated **SZ**
- Stainless steel, plain finish **NB**
- RoHS

Accessory

- Collar Nuts GN 53b → Page QVX

4

Information

T-slot bolts GN 52b fasten attachments and accessories in the slot of aluminum profiles. They are inserted into the slot of the aluminum profile at any position and affixed by a 90° turn.

The connection is conductive.

see also...

- Aluminum Profiles GN 10b (Profile Type Light) → Page QVX
- Aluminum Profiles GN 10b (Profile Type Heavy) → Page QVX

How to order

1 2 3 4  
**GN 52b-10 M8 30-SZ**

1	n
2	d
3	l <sub>1</sub>
4	Material / Finish

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9