



1

2

GN 530

d ₁	d ₂			d ₃	h	k	t min.
15	M 3	M 4	M 5	11	11	9	6
18	M 5	-	-	13	12	9	5
22	M 6	-	-	15	14	10	6
25	M 6	-	-	19	18	12	10
30	M 8	-	-	24	18	12	10
40	M 10	-	-	29	26	16	13
50	M 10	M 12	-	36	32	20	20

1

2

GN 530.5

d ₁	d ₂	d ₃	h	k	t min.
15	M 5	11	11	9	6
22	M 6	15	14	10	6
25	M 6	19	18	12	10
30	M 8	24	18	12	10

Specification

- Plastic
Duroplast (PF)
- Temperature resistant up to 110 °C
- Black, shiny finish
- **GN 530**
Bushing brass
- **GN 530.5**
Bushing
Stainless steel AISI 303
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

On request

- With threaded through bore
(with bushing brass)

Information

The surface quality of the knurled nuts GN 530 / 530.5 is of a sufficiently high standard to meet the highest requirements. The flash mark is not visible.

Duroplast material is highly resistant to chemicals.

How to order (Bushing brass)

GN 530-40-M10

1 d₁

2 d₂

How to order (Bushing stainless steel)

GN 530.5-22-M6

1 d₁

2 d₂