Knurled Nuts

Plastic, Threaded Bushing Stainless Steel





elesa
Original design B.259-CLEAN

STAIN LESS *

1 d1	2 d2	d3	h +0,5	k	t min.
22	M 6	13	25	13	12
25	M 8	16	28	14	13
32	M 10	19	32	15	17

Specification

3

Knob
Plastic, phenolic resin (PF)
- Operating temperature -20 °C to +110 °C
- White, RAL 9002, lacquered, shiny ○ **WS**

Threaded bushing
Stainless steel AISI 303

RoHS

The surface quality of the knurled nut GN 530.1 is of a sufficiently high standard to meet the highest requirements. The flash mark is not visible. Phenolic resin is highly resistant to chemicals.

Technical Information	Page
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order

GN 530.1-25-M8-WS (1 2 3)

1	d_1
2	d_2
3	Color