



¹ d ₁	² d ₂	³ Length l		d ₃	d ₄	h ₁	h ₂	t min.
50	M 10	20	50	23	27	84	62	17

Specification

- Plastic
Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 130 °C
 - Black, matte finish
- Color of the cover cap (shiny finish):
Orange, RAL 2004
- Bushing
Brass
- Threaded stud
Steel
Zinc plated, blue passivated
- *Plastic Characteristics* → Page 2158
- RoHS

On request

- Cover cap in black color

Information

Star knobs / Star knobs with threaded stud GN 5332 are used when circumstances dictate an extended shaft.

How to order (Bushing)

¹ ²
GN 5332-50-M10

1 d₁

2 d₂

How to order (Threaded stud)

¹ ² ³
GN 5332-50-M10-50

1 d₁

2 d₂

3 Length l