



STAIN
LESS
*

3 Type

- A Without bore
- E With threaded blind bore
- D With threaded through bore
- C With plain blind bore H7

1 d ₁	2 d ₂ Thread Type D Type E	2 d ₃ H7 Bore Type C	d ₄	h ₁	h ₂	t ₁ min.	t ₂
40	M 6	-	18	30,5	15	12	13
40	M 8	B 8	18	30,5	15	15	13
50	M 8	-	21	34	17	15	16
50	M 10	B 10	21	34	17	18	16
60	M 10	-	25	39	18	18	20
60	M 12	B 12	25	39	18	22	20

Specification

Stainless steel AISI 303

- Matte shot-blasted
- Highly polished (only type D / E)

4

PL

RoHS

Star knobs GN 5335 are a special development intended for the food processing machinery industry. The smooth and enclosed areas as well as the large corner radii comply with the requirements of hygiene standards.

see also...

	Page
GN 5339.5 Triangular Knobs	QVX
GN 5334 GN 5334.4 Star Knobs	QVX
GN 834 Wing Nuts	QVX
DIN 6336 Star Knobs	QVX
DIN 6335 Hand Knobs	QVX
GN 5345 Lobed Knobs	QVX

Technical Information

Cross holes GN 110 (Special Order)	QVX
ISO Fundamental Tolerances	QVX
Stainless Steel Characteristics	QVX

How to order (Matte shot-blasted)

GN 5335-40-M8-E

- 1** d₁
- 2** d₂ (d₃)
- 3** Type

How to order (Highly polished)

GN 5335-50-M10-E-PL

- 1** d₁
- 2** d₂ (d₃)
- 3** Type
- 4** Finish