

Type **C**



Type **E** (d_1 = 25 / 95)



elesa
Original design VCT.

Type **D**





Type **E** (d_1 = 32...84)



3 Type

- **E** With cover cap (Threaded blind bore)
- **C** With cover cap (Blind bore H9)
- **D** Without cover cap (Threaded through bore)

1 d_1	2 d_2 Type E			2 d_3 Type D			2 d_4 H9 Type C		d_5	d_6	h_1	h_2	t_1	t_2 min.
25*	M 4	M 5	M 6	-	-	-	-	-	13	8	19	8	10	-
32	M 5	M 6	M 8	M 5	M 6	M 8	B 6	-	15	10	23	10	12	12
40	M 6	M 8	-	M 6	M 8	-	B 8	-	17	13	27	12	18	14
40	M 10	-	-	M 10	-	-	-	-	17	13	27	12	17	-
50	M 8	M 10	M 12	M 8	M 10	M 12	B 8	B 10	19	15	32	14	20	14
63	M 8	M 10	M 12	M 8	M 10	M 12	B 8	B 10	22	19	37	16	26	20
74	M 12	M 14	-	M 12	M 14	-	B 8	B 12	26	17	43,5	22	26	20
74	M 16	-	-	M 16	-	-	B 16	-	26	17	43,5	22	31	20
84	M 12	M 16	-	M 12	M 16	-	B 12	B 16	28	22	44	21	25	25
95*	M 16	-	-	-	-	-	-	-	32	19	46	21	22	-

* only available in black (without cover cap)

Specification

4

Knob
Plastic, Polypropylen (PP)
- Reinforced, shock resistant
- Operating temperature 0 °C to +90 °C
- Black, matte finish

Bushing
- Brass for type E / D
- Steel for type C

Cover cap for type C / E
Plastic, Polypropylen (PP)

• Black, RAL 9005, matte finish	–
• Orange, RAL 2004, matte finish	DOR
• Gray, RAL 7035, matte finish	DGR
• Yellow, RAL 1021, matte finish	DGB
• Blue, RAL 5024, matte finish	DBL
• Red, RAL 3000, matte finish	DRT
• Green, RAL 6017, matte finish	DGN

RoHS

Characteristic of the star knobs GN 5337.2 is the 5 lobes. They not only give the knobs a specific style but this shape has also enabled the operator to achieve a higher torque.

see also...	Page
GN 5337.2 Star Knobs (Self Extinguishing)	QVX
GN 5337.7 Star Knobs (Threaded Bushing Stainless Steel)	QVX
GN 5337 Star Knobs (Phenolic Resin)	QVX
GN 5337.4 Star Knobs (Threaded Bushing Stainless Steel)	QVX
GN 5337.6 Star Knobs (Softline)	QVX
GN 5337.2 Star Knobs with Threaded Stud (with Loss protections GN 111.7)	QVX

Technical Information

ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX

How to order (Cover cap black)
1 2 3
GN 5337.2-40-M8-E

1	d_1
2	d_2 (d_3, d_4)
3	Type

How to order (Cover cap colored)
1 2 3 4
GN 5337.2-32-M5-E-DBL

1	d_1
2	d_2
3	Type
4	Color of the cover cap