



¹ d ₁	² d ₂		d ₃	h ₁	h ₂	t min.
43	M 6	M 8	17	29	11	12
53	M 8	M 10	19	34	13	17
66	M 10	M 12	21,5	38,5	15,5	17
77	M 12	-	26	46	21	20

Specification

- Base body
Plastic
Technopolymer (Polypropylen PP)
- Softline coating
 - Elastomer (TPE) 70 Shore A
 - Chemically bonded with base body
 - FDA compliant plastic granulate
 - Temperature resistant up to 80 °C
 - Black, matte finish
- Color of the cover cap (matte finish):
 - Black, RAL 9005
 - Orange, RAL 2004
 - Gray, RAL 7035
 - Yellow, RAL 1021
 - Blue, RAL 5024
 - Red, RAL 3000
 - Green, RAL 6017



Information

The softline coating makes the star knobs GN 5337.6 particularly user-friendly and ergonomic.

The **soft, slip-proof** contact area improves the contact both in hot (hand perspiration) and in dry ambient conditions, in the event of oily surfaces and even high or low temperatures.

The use of Softline star knobs is recommended particularly when heavy duty clamping is required.

see also...
• *Product Family Softline®* → Page 18

- -
- DOR
- DGR
- DGB
- DBL
- DRT
- DGN

- Bushing
Brass
- *Elastomer Characteristics* → Page 2158
- *Plastic Characteristics* → Page 2158
- RoHS

How to order (Cover cap black)	¹ ²	d ₁
		d ₂
GN 5337.6-43-M8		

How to order (Cover cap colored)	¹ ² ³	d ₁
		d ₂
		Color of the cover cap
GN 5337.6-53-M10-DRT		