



1.1

1.2

1.3

1.4

d₁	d₂	Length l				d₃	h₁	h₂
43	M 6	16	20	25	30	17	29	11
43	M 8	16	20	25	30	17	29	11
53	M 8	16	20	30	40	19	34	13
53	M 10	20	30	40	50	19	34	13
66	M 10	20	30	40	50	21,5	38,5	15,5
66	M 12	30	40	50	-	21,5	38,5	15,5
77	M 12	30	40	50	-	26	46	21

2.1

Specification

- Base body
Plastic
Technopolymer (Polypropylen PP)
- Softline coating
- Elastomer (TPE) 70 Shore A
- Chemically bonded with base body
- FDA compliant plastic granulate
- Temperature resistant up to 80 °C
- Black, matte finish
- Color of the cover cap
Black, RAL 9005, matte finish
- Threaded stud
Steel
Zinc plated, blue passivated
- *Plastic Characteristics* → Page 2158
- RoHS

Information

The softline coating makes the star knobs with threaded stud GN 5337.6 particularly user-friendly and ergonomic.

The **soft, slip-proof** contact area improves the contact both in hot (hand perspiration) and in dry ambient conditions, in the event of oily surfaces and even high or low temperatures.

The use of star knobs with threaded stud is recommended particularly when heavy duty clamping is required.

see also...

- *Product Family Softline®* → Page 18

2.2

2.3

On request

- Cover caps in other colors

How to order	
1	d ₁
2	d ₂
3	Length l

GN 5337.6-53-M10-30



2.4