

STAINLESS *

3 Type

E With threaded blind bore
D With threaded through bore
C With plain blind bore H7

1 d_1	2 d_2 Thread Type E / D	2 d_3 H7 Bore Type C	d_4	h_1	h_2	t_1 min.	t_2
25	M 5	-	12	16	8	10	11
32	M 6	-	15	21	11	12	13
40	M 6	-	18	26	15	12	13
40	M 8	B 8	18	26	15	15	13
50	M 8	-	21	30	17	15	16
50	M 10	B 10	21	30	17	18	16
60	M 10	-	25	35	18	18	20
60	M 12	B 12	25	35	18	22	20

Specification

GN 5345
Stainless steel AISI 303
Matte shot-blasted

GN 5345.4
Stainless steel AISI 316L
Matte shot-blasted

RoHS

On request

- Highly polished (PL) (only type D and E)

Three-lobed knobs GN 5345 / GN 5345.4 have a smooth and sealed surface. They are particularly suitable for use where hygiene requirements are high. Their shape allows relatively high torques to be applied.

see also...	Page
DIN 6336 Star Knobs	QVX
DIN 6335 Hand Knobs	QVX
GN 5334 Star Knobs	QVX
GN 835 Wing Screws	QVX

Technical Information

Cross holes GN 110 (Special Order)	QVX
ISO Fundamental Tolerances	QVX
Stainless Steel Characteristics	QVX

How to order (Stainless steel AISI 303)
1 2 3
GN 5345-60-B12-C

1	d_1
2	d_3 (d_2)
3	Type

How to order (Stainless steel AISI 316L)
1 2 3
GN 5345.4-40-M8-E

1	d_1
2	d_2 (d_3)
3	Type