Knurled Screws

Plastic, Threaded Stud Steel







elesa
Original design MBT-p



1 d1 Nominal dimension	d1 Actual dimension	2 d2	3 Length l						d3	h1	h2
32	31	M 5	10	20	40	-	-	-	15	24	11,5
32	31	M 6	10	16	20	25	30	40	15	24	11,5
40	39,5	M 6	10	16	20	30	40	-	17	26,5	12,5
40	39,5	M 8	16	20	25	30	40	50	17	26,5	12,5
50	50	M 8	16	30	50	-	-	-	20	33	16
50	50	M 10	20	30	50	-	-	-	20	33	16
60	61	M 10	20	30	50	-	-	-	23	39	18,5
60	61	M 12	20	30	50	-	-	-	23	39	18,5
70	70	M 12	30	50	-	-	-	-	24	42	20,5

Specification

4 5

Knob
Plastic, Polypropylen (PP)
- Reinforced, shock resistant
- Black, RAL 9005, matte finish ● **SW**

Threaded stud
Steel
Zinc plated, blue passivated

Cover cap
Plastic, Polyamide (PA)
- Black, RAL 9005, matte finish ● –
- Orange, RAL 2004, matte finish ● **DOR**
- Gray, RAL 7035, matte finish ● **DGR**
- Yellow, RAL 1021, matte finish ● **DGB**
- Blue, RAL 5024, matte finish ● **DBL**
- Red, RAL 3000, matte finish ● **DRT**
- Green, RAL 6017, matte finish ● **DGN**

Operating temperature 0 °C to +90 °C

RoHS

The unique profile on the rim (small squares) of the knurled screws GN 534 is characteristic of its form and the function.

see also...	Page
GN 7336 Knurled Screws	QVX
GN 4534 Knurled Knobs with Threaded Stud (Softline)	QVX
GN 534 Knurled Screws (with Loss protections GN 111.7)	QVX

Technical Information

Plastic Characteristics	QVX

How to order (Cover cap black)

1 2 3 4
GN 534-60-M12-30-SW

1	d_1
2	d_2
3	Length l
4	Color (Knob)

How to order (Cover cap colored)

1 2 3 4 5
GN 534-32-M6-30-SW-DRT

1	d_1
2	d_2
3	Length l
4	Color (Knob)
5	Color (Cover cap)