



1 d_1		2 d_2	3 Length l						d_3	h_1	h_2
Nominal dimension	Actual dimension										
32	31	M 5	10	20	40	-	-	-	15	24	11,5
32	31	M 6	10	16	20	25	30	40	15	24	11,5
40	39,5	M 6	10	16	20	30	40	-	17	26,5	12,5
40	39,5	M 8	16	20	25	30	40	50	17	26,5	12,5
50	50	M 8	16	30	50	-	-	-	20	33	16
50	50	M 10	20	30	50	-	-	-	20	33	16
60	61	M 10	20	30	50	-	-	-	23	39	18,5
60	61	M 12	20	30	50	-	-	-	23	39	18,5
70	70	M 12	30	50	-	-	-	-	24	42	20,5

Specification

- Plastic Technopolymer (Polypropylen PP)
 - Reinforced, shock-resistant
 - Temperature resistant up to 90 °C
 - Black, RAL 9005, matte ● **SW**
- Threaded stud Steel
Zinc plated, blue passivated
- Color of the cover cap (matte finish):
 - - Black, RAL 9005
 - **DOR** Orange, RAL 2004
 - **DGR** Gray, RAL 7035
 - **DGB** Yellow, RAL 1021
 - **DBL** Blue, RAL 5024
 - Red, RAL 3000
 - **DRT** Green, RAL 6017
 - **DGN**
- *Plastic Characteristics* → Page 2158
- **RoHS**

Information

The unique profile on the rim (small squares) of the knurled screws GN 534 is characteristic of its form and the function.

see also...

- *Knurled Screws GN 7336* → Page 626
- *Knurled Knobs GN 4534 (Softline)* → Page 624
- *Knurled Screws GN 534 with Loss Protection GN 111.7* → Page 2084

How to order (Cover cap black)

1	d_1
2	d_2
3	Length l
4	Color (Knob)

GN 534-60-M12-30-SW

How to order (Cover cap colored)

1	d_1
2	d_2
3	Length l
4	Color (Knob)
5	Color (Cover cap)

GN 534-32-M6-30-SW-DRT

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

