



d₁	d₂	d₃	d₄	h₁	h₂	t_{min.}
40	M 6	18	18,8	30,5	15	12
40	M 8	18	18,8	30,5	15	15
50	M 8	21	21,8	34	17	15
50	M 10	21	21,8	34	17	18

Specification

- Stainless steel AISI 316L
 - Matte finish (Ra < 0,8 µm) **MT**
 - Polished finish (Ra < 0,8 µm) **PL**
- Sealing ring
 - H-NBR **H**
Temperature resistant -25 °C to +150 °C
 - EPDM **E**
Temperature resistant -40 °C to +120 °C
 - Blue
 - Hardness 85±5 Shore A
 - FDA compliant
- Plastic Characteristics → Page 2158
- Stainless Steel Characteristics → Page 2166
- RoHS

Accessory

- Sealing Rings GN 7600 → Page 1596

On request

- with FKM sealing ring (Fluorine rubber) **F**

Information

Star knobs GN 5435 are intended for use in hygienic areas. The sealed mounting surface enables fastening without dead spaces. The high quality finish and the large corner radii prevent adherence of dirt and facilitate cleaning.

see also...

- Product Family *Hygienic Design* → Page 16
- Three Lobe Knobs GN 5445 (Stainless Steel, *Hygienic Design*) → Page 593
- Adjustable Hand Levers GN 305 (Stainless Steel, *Hygienic Design*) → Page 442

How to order

1	d₁
2	d₂
3	Finish
4	Material (Sealing ring)

GN 5435-40-M8-PL-H

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4