



- 3 Type**
- A** Mounting from the back (threaded blind bore)
  - B** Mounting from the operator's side

<b>1</b> b	<b>2</b> l <sub>1</sub> ±0,25	l <sub>2</sub> Type A	l <sub>3</sub> ≈ Type B	a	d <sub>1</sub>	d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub>	r	t min.
20	120	142	137	13	M 5	5,3	41	5	13	10
20	160	182	177	13	M 5	5,3	45	5	13	10

**Specification**

- Aluminum
    - Powder coated
      - Black, RAL 9005, textured finish
      - Silver, RAL 9006, textured finish
    - Anodized, natural color
    - Plain, tumbled
- **Load Rating Information** → Page 2106
- **RoHS**

- **SW**
- **SR**
- **EL**
- **BL**

**Information**

Cabinet U-handles GN 565.3 are manufactured from a bent aluminum profile. They are suitable for applications where lower lifting forces are required such as on lids or protective machine covers.

The countersunk holes of type B allow fixing with self tapping screws or countersunk rivets.

How to order	
<b>1</b>	b
<b>2</b>	l <sub>1</sub>
<b>3</b>	Type
<b>4</b>	Finish

**GN 565.3-20-120-B-SW**

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4