



ROSTFREI
Inox
Stainless
Steel

3 Type

- A** Mounting from the back (threaded blind bore)
- B** Mounting from the operator's side

1

2

b		$l_1 \pm 0,25$	$l_2 \approx$	a	d_1 Type A	d_2 Type B	$h_1 \approx$	h_2	t_1 min.	t_2
GN 565.4	GN 565.9									
20	20	160	185	13	M 6	5,3	50	5	8	5
20	20	192	221	13	M 6	5,3	50	5	8	5
26	-	160	190	17	M 8	6,4	57	6	11	6
26	-	192	227	17	M 8	6,4	57	6	11	6

Specification

4

GN 565.4

Aluminum

- Powder coated

Black, RAL 9005, textured finish

Red, RAL 3000, textured finish

Silver, RAL 9006, textured finish

- Anodized, natural color

- Plain, tumbled

- **SW**
- **RS**
- **SR**
- **EL**
- **BL**

GN 565.9

Stainless steel AISI 304

Matte shot-blasted

MT

• *Load Rating Information* → Page 2106

• *Stainless Steel Characteristics* → Page 2166

• **RoHS**

Information

The manufacturing process (bending) allows the production of **special lengths** in relatively small quantities.

see also...

• *Arch Handles GN 665 (Aluminum, Ellipse Profile)* → Page 166

• *Arch Handles GN 424.1 (Steel, Ø10)* → Page 167

• *Stainless Steel Arch Handles GN 424.5 (Ø10)* → Page 167

How to order (Aluminum)

1	b
2	l_1
3	Type
4	Finish

GN 565.4-20-160-B-RS

How to order (Stainless steel)

1	b
2	l_1
3	Type
4	Finish

GN 565.9-20-192-A-MT