



- 3 Type**
- A** Mounting from the back (threaded blind bore)
 - B** Mounting from the operator's side

1 b		2 l₁	a	d₁ Type A	d₂ Type B	h₁ ≈	h₂	l₂ ≈	t₁ min.	t₂
GN 565.4	GN 565.9									
20	20	160	13	M 6	5,3	50	5	185	8	5
20	20	192	13	M 6	5,3	50	5	221	8	5
26	-	160	17	M 8	6,4	57	6	190	11	6
26	-	192	17	M 8	6,4	57	6	227	11	6

Specification

GN 565.4

Aluminum

- Powder coated
 - Black, RAL 9005, textured finish
 - Red, RAL 3000, textured finish
 - Silver, RAL 9006, textured finish
- Anodized, natural color
- Plain finish, tumbled

- **SW**
- **RS**
- **SR**
- **EL**
- **BL**

GN 565.9

Stainless steel AISI 304

Matte shot-blasted finish

MT

RoHS

see also...

	Page
GN 665 Arch Handles (Aluminum, ellipse profile)	QVX
GN 424.1 Arch Handles (Steel, Ø 10)	QVX
GN 424.5 Arch Handles (Stainless Steel, Ø 10)	QVX

Technical Information

Load Rating Information	QVX
Stainless Steel Characteristics	QVX

How to order (Aluminum)	
1 b	
2 l₁	
3 Type	
4 Finish	
GN 565.4-20-160-B-RS	

How to order (Stainless Steel)	
1 b	
2 l₁	
3 Type	
4 Finish	
GN 565.9-20-192-A-MT	