



**elesa**  
Original design BT.S-p-INOX

**ROSTFREI**  
Inox  
Stainless  
Steel

1.1  
1.2  
1.3  
1.4

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub>	Length l			<sup>3</sup> d <sub>3</sub>	h	k
20	M 5	10	16	-	12	16	10
25	M 6	16	20	30	16	19	11
32	M 8	16	20	30	17	22	13

**Specification**

- Plastic  
Technopolymer (Polyamide PA)  
- Reinforced  
- Temperature resistant up to 130 °C  
- Black, matte finish
- Threaded stud  
Stainless steel AISI 303
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

**Information**

- see also...
- *Knurled Screws GN 421* → Page 637
  - *Knurled Screws GN 591 (Threaded Stud Steel)* → Page 633

2.1  
2.2  
2.3  
2.4

How to order	<sup>1</sup> d <sub>1</sub>
	<sup>2</sup> d <sub>2</sub>
	<sup>3</sup> Length l
<b>GN 591.5-20-M5-16</b>	

