



Inox  
Stainless  
Steel



d <sub>1</sub>	GN 598.3	GN 598.5	d <sub>2</sub>	d <sub>3</sub>	l <sub>1</sub> ≈	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub> ≈	l <sub>5</sub>
18	-	-	M 5	16	57	15	5	52	9,5
21	-	-	M 5	16	67	15	5	62	9,5
22	-	-	M 5	16	73	15	5	68	9,5
23	23	-	M 6	20	87	19,5	6	80	10,5
26	26	-	M 6	20	102	19,5	6	95	10,5
28	28	-	M 8	26	118	26	10	106	16

**Specification**

- Handle  
Plastic  
Duroplast (Phenolic PF)  
- Temperature resistant up to 110 °C  
- Black, shiny finish  
- Revolving

- **GN 598.3**  
Retractable mechanism  
Steel  
Blackened

- **GN 598.5**  
Retractable mechanism  
Stainless steel  
- Spindle  
AISI 303  
- Flat base  
Sintered steel AISI 316LHC

- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS



**Information**

**KU**

Retractable handles GN 598.3 / GN 598.5 are used when the handle should not protrude temporarily for space or safety reasons.

see also...

- *Safety Retractable Handles GN 798.7 (Automatic Return to the Retracted Position, Steel)* → Page 53
- *Safety Retractable Handles GN 798.8 (Automatic Return to the Retracted Position, Stainless Steel)*

→ Page 53

How to order (Retractable mechanism steel)

**GN 598.3-KU-26**

1	Material
2	d <sub>1</sub>

How to order (Retractable mechanism SST)

**GN 598.5-KU-23**

1	Material
2	d <sub>1</sub>