



1			2			3							
l_1	d_1 Thread			d_2 H7 Bore		d_3	d_4	h_1	h_2	h_3	h_4 Stroke	t min.	
44	M 4	M 5	M 6	B 5	B 6	10	15,5	24,5	3,5	30,5	3,5	8	
63	M 6	M 8	-	B 8	-	13,5	19	31	3,5	38,5	4	10	
78	M 8	M 10	M 12	B 8	B 10	16	23	36	3,5	46,5	4	14	
95	M 10	M 12	-	B 12	-	19	26,5	43	5	56,5	4	17	

Specification

- Handle
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 130 °C
- Black-gray, RAL 7021, matte ● **SG**
- Orange, RAL 2004, matte ● **OR**
- Annular gear ring
Zinc die casting
- Bushing and retaining screw
Steel, blackened
- ISO Fundamental Tolerances → Page 2151
- Plastic Characteristics → Page 2158
- RoHS

Information

Adjustable hand levers GN 604 like all the products of the Ergostyle® family are renowned for their good style but also their ergonomic shape.

Pulling the lever disengages the serration and allows it to be turned in either direction to reach the ideal new location. On releasing the handle the serrations re-engage automatically.

see also...

- Product Family Ergostyle® → Page 18
- Adjustable Hand Levers GN 604.1 (Plastic, Bushing Stainless Steel) → Page 462
- Adjustable Hand Levers GN 602 (Zinc Die Casting, Bushing Steel) → Page 456

How to order

GN 604-44-M6-SG

- 1 l_1
- 2 d_1 (d_2)
- 3 Color