



elesa
Original design M.843

1

Length l	d	a	b	h	t min.
86 ±0,5	M 6	17	26	46,5	12
117 ±0,5	M 8	20	30	53	13
179 ±1,0	M 8	20	30	62	13
300 ±1,0	M 8	22	32	64	13

Specification

2

Handle

Plastic, Polyamide (PA)

• Operating temperature -20 °C to +110 °C

• Color

- Black, RAL 9005, shiny finish
- Orange, RAL 2004, shiny finish
- Red, RAL 3000, shiny finish
- Yellow, RAL 1021, shiny finish
- Gray, RAL 7040, shiny finish
- Blue, RAL 5024, shiny finish
- Green, RAL 6017, shiny finish
- White, RAL 9002, shiny finish

- SW
- OR
- RT
- GB
- GR
- BL
- GN
- WS

Threaded bushings

- Brass
- Stainless steel for WS

RoHS

Cabinet U-handles GN 625 have a very ergonomic elliptical profile and the surface is smooth and shiny.

see also...

	Page
GN 525 Cabinet U-Handles (Phenolic Resin)	QVX
GN 565 Cabinet U-Handles (Aluminum)	QVX
GN 725 Cabinet U-Handles (Polypropylene)	QVX

Technical Information

Strength Properties	QVX
Plastic Characteristics	QVX

How to order

GN 625-117-RT

1 Length l

2 Color