



d ₁	d ₂	d ₃	l ₁	l ₂	l ₃ min.
M 10	18	8	80	60	20
M 12	20	10	100	70	25
M 16	24	12	120	85	35
M 20	30	16	140	95	40

Specification

- Steel
Property class 5
Blackened
- *Strength Values of Nuts* → Page 2152
- RoHS

Information

see also...

- *Quick Release Toggle Nuts GN 6305.1 (Steel, Zinc Plated)* → Page 514

How to order

DIN 6305-M16

1 d₁