



$d_1$	$d_2$	$d_3$	$d_4$	$l_1 \approx$	$l_2$	$l_3 \approx$
M 10	24	10,5	8	68	30	20
M 12	26	13	9	82	36	24,5
M 16	32	17	10	98	45	32

Specification

- Steel  
zinc plated, blue passivated
- Butt-welded toggle
- RoHS

On request

- in Stainless Steel

Information

Quick release toggle nuts GN 6336.3 are used in such applications where the knob has to be completely removed after the releasing operation and refitted rapidly for re-clamping.

Plug the toggle nut onto the threaded bolt at an oblique angle. During the clamping action, it engages into the threads of the bolt.

see also...

- Quick release knurled nuts GN 6303.1 → Page 462
- Quick release star knobs GN 6336.3 → Page 404

How to order	1	$d_1$
	2	Material